



DFN-24 to DIP-28 SMT Adapter (0.5 mm pitch, 7.0 x 4.0 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		3.10				
B		0.70				
C		0.25				
B2		2.64				
C2		6.43				
D		0.25				
D2		0.23				
E		0.50				
F					0.600	
G					0.100	
H					0.025	




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)