


## DFN-6 to DIP-10 SMT Adapter (0.65 mm pitch, 2.0 x 2.1 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		1.40				
B		0.55				
C		0.30				
B2		0.65				
C2		1.35				
D		0.35				
D2		0.375				
E		0.65				
F					0.600	
G					0.100	
H					0.025	

Top View (SMT Footprint)



(Representative drawing only - not to scale)

### Bottom View (DIP Pins)



(Representative drawing only - not to scale)

### Side View (DIP Pins)



(Representative drawing only - not to scale)