

DFN-8 to DIP-12 SMT Adapter (0.8 mm pitch, 4.0 x 4.0 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		3.00				
B		0.70				
C		0.30				
B2		2.20				
C2		3.00				
D		0.50				
D2		0.40				
E		0.80				
F					0.600	
G					0.100	
H					0.025	

Top View (SMT Footprint)



(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)