

MTA 45 MF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

General ordering data

Version	Electronics housings, Mounting flange
Order No.	1251310000
Type	MTA 45 MF
GTIN (EAN)	4050118042719
Qty.	1 pc(s).

MTA 45 MF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	10.5 mm	Height (inches)	0.413 inch
Width	47 mm	Width (inches)	1.85 inch
Length	97.3 mm	Length (inches)	3.831 inch
Net weight	97 g		

General data

Weight	97 g
--------	------

Classifications

ETIM 6.0	EC002625	ETIM 7.0	EC002625
ETIM 8.0	EC002625	ECLASS 9.0	27-18-28-07
ECLASS 9.1	27-04-92-90	ECLASS 10.0	27-18-28-07
ECLASS 11.0	27-18-28-07	ECLASS 12.0	27-18-28-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	