





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			D	REVISED PER ECR-07-012448	31JUL07	HMR
						APVD
						GJ

- 1 SPECIFICATIONS:
MAGNET WIRE #27 - #36 AWG,
.015" (0.38mm) - .005" (0.13mm) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION: #1601425
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO
ELECTRONICS SPECIFICATION 114-13166 FIGURE 6.



-	-	-
-	-	-
-	-	-
-	-	-
-	-	-
PRE-TIN PLATE OVER COPPER UNDERPLATE	150-031-014	1601133-2
FINISH	REFERENCE PART NUMBER	TYCO PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002	Tyco Electronics Corporation Harrisburg, PA 17105-3608
DIMENSIONS: INCHES	PRODUCT SPEC 108-2244 APPLICATION SPEC 3	NAME FINE RANGE WIRE TO .110 X .032 MULTI-BARB TAB SIAMEZE TERMINAL
MATERIAL BRASS, 1/2 HARD	WEIGHT -	SIZE A2 CAGE CODE 00779 DRAWING NO C-1601133
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± - ANGLES ± 2° FINISH SEE TABLE	CUSTOMER DRAWING	RESTRICTED TO -
SCALE 1:6		SHEET 1 of 1 REV D