

# Actuator

45-  
2844.4C90.006



<https://eao.com/p/45-2844.4C90.006>

Your product:

---



## 45-2844.4C90.006 Actuator

### FRONT

Front dimension:	Ø 38 mm
Front bezel colour:	Sand grey
Front bezel material:	Metal

### MOUNTING

Design:	flush
---------	-------

### OPERATING-/INDICATION PART

Lever colour:	White
Lever shape:	short
Lever material:	plastic

### MECHANICAL CHARACTERISTIC

Weight:	0.062 kg
Switching action:	Rest - Momentary
Switching positions:	2 positions
Switching angle:	45° right
Mechanical lifetime:	1 Mio. cycles of operation
Operating frequency:	1 800/h

### AMBIENT CONDITION


IP front protection:	IP66, IP67, IP69K
----------------------	-------------------

<b>Operating temperature:</b>	– 25 °C ... + 70 °C
<b>Storage temperature:</b>	– 40 °C ... + 80 °C
<b>Climate resistance:</b>	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6
<b>Vibration resistance:</b>	According to IEC 60068-2-6: 10 ... 500 Hz: 5 g
<b>Shock resistance:</b>	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms


## OTHER

<b>Housing material:</b>	Metal
<b>Hints:</b>	Front panel thickness 1 ... 6 mm
<b>Short Description:</b>	Actuator, Ø 38 mm, optional illuminative, White, short, Sand grey, Metal, Rest - Momentary, IP66, IP67, IP69K

## Dimension drawings:



## Switching positions:



Wiring diagrams:

