




Scotchlok™ Terminals

MVU18BC, MVU14BC, MVU10BC

Butt Connector, Vinyl Insulated, Butted Seam



Data Sheet

Product Number	Wire Range (AWG)	L	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter
MVU18BC	22-18	1.00	0.030	0.25	0.070	0.145
MVU14BC	16-14	1.00	0.030	0.25	0.090	0.170
MVU10BC	12-10	1.02	0.040	0.25	0.135	0.250



UNDERWRITERS
LABORATORIES
STANDARD NO. UL 486C
3M FILE NO. E23438



CANADIAN STANDARDS
ASSOCIATION
STANDARD NO. 22.2
NO. 0, 65
3M FILE NO. LR22190

Installation Information

⚠ WARNING


Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end 5/16 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style) or TR-490 (ratchet style) hand tools.



 Barrel Crimp (Required)

Specifications

Wire Size:
Barrel Seam:
Insulator Max. Volt Rating:

Maximum Operating Temp.:
Maximum Current:
Insulator Material:
Terminal Material:
Terminal Plating:

See Table Above
Butted
600 V Building Wire:
1000 V Signs or
Fixtures (Luminaires)
221°F (105°C)
Same as Wire
Vinyl
ETP Copper
Tin

3M is a trademark of 3M Company.



is a trademark of Underwriters Laboratories.



is a trademark of Canadian Standards Association.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, Indirect, special, Incidental or consequential regardless of the legal theory asserted.**



Electrical Markets Division

6801 River Place Blvd.

Austin, TX 78726-9000

www.3M.com/electrical

Litho in USA

© 3M 2004 78-8125-9668-8-B