



Terminal verpresst
Terminal pressed






Leiterplatte
PCB


Leiterplatten-Layout Vorschlag
PCB-Layout Proposal



Verpackt im Gurt nach DIN IEC 60286-3
Tape on Reel Packaging according to DIN IEC 60286-3
Verpackungseinheit: 2000 Stück
Packaging unit: 2000 pcs




Abspulrichtung - *Reel off Direction* →




Montagehinweis
Assembly Instruction

Es ist darauf zu achten, dass das Kabel senkrecht ($90^\circ \pm 5^\circ$) abgeschnitten wird!
It is important to ensure that the cable is cut off perpendicular ($90^\circ \pm 5^\circ$)!



richtig
correct



falsch
false



*AWG 24/7 - 26/7 D 1.1 mit Kabelanschlag
**AWG 24/7 - 26/7 D 1,1 with cable stop*

Information: Farbe: schwarz color: black		Tolerances		Scale	10:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation Schneidklemmterminal* IDC-Terminal*	
		www.ERNI.com		474341	
a	19.03.2015			I	
Index	Date			A3	
		Class		IDC-TERM	