

偶数極6,8,10極
EVEN NUMBER Pos.6,8,10 Pos.
(SCALE 5-1)

嵌合相手製品型番及び、嵌合時寸法は
MATING COUNTER PART NUMBER AND DIMENSIONS
表-1 参照のこと。
AFTER MATING: SEE TABLE 1.

嵌合時寸法: 巾(mm)×高さ(mm)
DIMENSIONS AFTER MATING : WIDE(mm) × HEIGHT(mm)

MATING COUNTER CONN 嵌合相手側コネクタ POST HDR ASSY			SMT-Y TYPE WITH BOSS X-174637-X	
製品型番			P/N	高さ H
DIP TYPE	X-174642-X		3.95	4.4 (巾) W x 5.1 (高さ) H
			5.95	4.4 (巾) W x 7.0 (高さ) H
SMT TYPE	ボス無 X-174644-X WITHOUT BOSS ボス付 X-174820-X WITH BOSS		3.95	4.4 (巾) W x 5.1 (高さ) H
			5.95	4.4 (巾) W x 7.1 (高さ) H



TABLE 1 SMT TYPEは、巾及び高さ寸法に
SMT TYPE INCLUDE DIMENSIONS
半田付タイン部寸法を含みます。
OF SOLDER DIP TYPE.

△2 基板位置決め用ボス切断跡。
CUT MARK OF POSITIONER BOSS.


△3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△4 OBSOLETE PARTS

13 225



20種 20Pos.
(SCALE 5-1)



TE Connectivity



TE Connectivity

1.25 F-P CONNECTOR (B-TO-B)
SINGLE ROW REC HDR ASS'Y (V) SMT TYPE
WITH BOSS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A300779C-174637

SCALE	10:1	SHEET	1 OF 1	REV	M1
-------	------	-------	--------	-----	----

CUSTOMER DRAWING

CUSTOMER DRAWING

AS SHOWN

AS SHOWN

MATERIAL


SH

AS SHOWN
圖中參照

AS SHOWN
图中参照

鉛フリー
LEAD FREE

17極 17Pos.
(SCALE 5-1)



SECT "B"-"B"

REC HEADER HOUSING
リセ・ヘッダー・ハウジング
PPS
(11194V-0)

リセ・CONTACT

(ニッケル下地 錫めっき仕上げ 焼青銅)
 POST TIN PL.
 (Ni UNDER PL. ALL OVER Phos-Broz)
 板厚: 0.3t
 THK: 0.3t

ボス形状 'B'
BOSS FORM 'B'

ボス形状 'A'
BOSS FORM 'A'

(NON ACCUMULATE) ±0.1
非累積公差

HOUSING EXTERNAL FORM
ハウジング外形

$\phi 0.8$
 コネクタ
 CONNECTOR
 決め用穴
 POSITIONER HOLE

P.C.B MOUNTING LAYUOUT

(最小) (適用基板厚 : 0.6mm 最小)
(MIN) (APPLICABLE P.C.B THK : 0.6mm MIN)