



DESCRIPTION: M5 FEMALE - PANEL MOUNT (REAR) - VERTICAL - 4 POSITION



NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

SHELL:

BRASS

O-RING:

NBR, BLACK

FINISH

CONTACT:

GOLD PLATED

OVER 50 μ NICKEL

NUT:

NICKEL PLATED

SHELL:

NICKEL PLATED

ELECTRICAL

RATED CURRENT:

1A

RATED VOLTAGE:

60V

INSULATION RESISTANCE:

100 M Ω hms MIN.

CONTACT RESISTANCE:

10 m Ω hms MAX..

WATER PROOF:

IP67





ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C

852-004-213R00Y

- 1 = GOLD FLASH
4 = 10 μ " GOLD
2 = 30 μ " GOLD



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
5

DWG NO.

852-004-213R00Y