

| REVISIONS |     |                 |           |     |      |
|-----------|-----|-----------------|-----------|-----|------|
| P         | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|           | A   | INITIAL RELEASE | 22MAY2015 | GY  | CW   |
|           | A1  | ECR-18-011999   | 01AUG2018 | WQR | CW   |
|           | A2  | ECR-18-009564   | 19SEP2018 | CD  | CW   |
|           | B   | ECR-20-011774   | 30APR2021 | BS  | CW   |

NOTES:  
1. TECHNICAL CHARACTERISTICS:  
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY  
SURFACE TREATMENT: SEE TABLE  
DEGREE OF PROTECTION: IP68 (MATED)




注 释

1. 技术参数：


壳体材料： 铝合金

表面处理： 见表格

防护等级： IP68 （配合）



WITHOUT THE LOGO-



THIS TYPE IS SAME AS TYPE I, ONLY NO LOGO  
此类型同类型I, 只是无LOGO

|                                                                                       |  |                                                                                                                                                        |  |                                                                                                       |                |
|---------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN 21MAY2015<br>Gino.Yao<br>CHK 21MAY2015<br>Chris.Wang<br>APVD 21MAY2015<br>Xiang.Xu<br>PRODUCT SPEC<br>108-137014<br>APPLICATION SPEC<br>114-137014 |  |  TE Connectivity |                |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES, UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.<br>1 PLC ±.<br>2 PLC ±.<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±.<br>FINISH                             |  | NAME<br>H6BPR-TGHC-PG/M                                                                               |                |
|  |  | WEIGHT<br>-                                                                                                                                            |  | SIZE<br>A2                                                                                            | CAGE CODE<br>- |
| MATERIAL<br>-<br>-                                                                    |  | CUSTOMER DRAWING<br>Customer Drawing                                                                                                                   |  | DRAWING NO<br>C-T192206XXXXX00                                                                        |                |
|                                                                                       |  | SCALE<br>1:1                                                                                                                                           |  | SHEET<br>1 OF 2                                                                                       |                |
|                                                                                       |  |                                                                                                                                                        |  | RESTRICTED TO<br>-<br>REV B                                                                           |                |

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |

NOTE:

SEE SHEET 1

注释:

见页1

|                   |                                          |                        |                                                                                                               |                        |              |
|-------------------|------------------------------------------|------------------------|---------------------------------------------------------------------------------------------------------------|------------------------|--------------|
| TI922062116-001   | POWDER COATED, DEEP GREY<br>表面喷涂, 深灰色    | H6BPR-TGHC-PG16        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG16,POWDER COATED,DEEP GREY,NO LOGO<br>H6BPR上壳,中部锁定,顶出PG16,深灰色粉末喷涂,无LOGO | PG16                   | TYPE2<br>类型2 |
| TI922062125-001   | POWDER COATED, DEEP GREY<br>表面喷涂, 深灰色    | H6BPR-TGHC-M25         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M25,POWDER COATED,DEEP GREY,NO LOGO<br>H6BPR上壳,中部锁定,顶出M25,深灰色粉末喷涂,无LOGO   | M25                    |              |
| TI922062132-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-M32         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M32,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出M32,灰色粉末喷涂                       | M32                    |              |
| TI922062129-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-PG29        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出PG29,灰色粉末喷涂                     | PG29                   | TYPE1<br>类型1 |
| TI922062125-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-M25         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M25,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出M25,灰色粉末喷涂                       | M25                    |              |
| TI922062121-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-PG21        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出PG21,灰色粉末喷涂                     | PG21                   |              |
| TI922062120-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-M20         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M20,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出M20,灰色粉末喷涂                       | M20                    |              |
| TI922062116-000   | POWDER COATED, GREY<br>表面喷涂, 灰色          | H6BPR-TGHC-PG16        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG16,POWDER COATED,GREY<br>H6BPR上壳,中部锁定,顶出PG16,灰色粉末喷涂                     | PG16                   |              |
| TI922061140-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-M40         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M40,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出M40,银白色粉末喷涂              | M40                    |              |
| TI922061132-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-M32         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M32,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出M32,银白色粉末喷涂              | M32                    |              |
| TI922061129-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-PG29        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出PG29,银白色粉末喷涂            | PG29                   |              |
| TI922061125-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-M25         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M25,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出M25,银白色粉末喷涂              | M25                    |              |
| TI922061121-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-PG21        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出PG21,银白色粉末喷涂            | PG21                   |              |
| TI922061120-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-M20         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M20,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出M20,银白色粉末喷涂              | M20                    |              |
| TI922061116-000   | POWDER COATED, SILVER WHITE<br>表面喷涂, 银白色 | H6BPR-TGHC-PG16        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG16,POWDER COATED,SILVER WHITE<br>H6BPR上壳,中部锁定,顶出PG16,银白色粉末喷涂            | PG16                   |              |
| TI922060140-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-M40         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M40,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出M40,黑色粉末喷涂                      | M40                    |              |
| TI922060132-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-M32         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M32,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出M32,黑色粉末喷涂                      | M32                    |              |
| TI922060129-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-PG29        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出PG29,黑色粉末喷涂                    | PG29                   |              |
| TI922060125-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-M25         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M25,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出M25,黑色粉末喷涂                      | M25                    |              |
| TI922060121-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-PG21        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出PG21,黑色粉末喷涂                    | PG21                   |              |
| TI922060120-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-M20         | H6BPR HOOD,CENTER LOCKING,TOP ENTRY M20,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出M20,黑色粉末喷涂                      | M20                    |              |
| TI922060116-000   | POWDER COATED, BLACK<br>表面喷涂, 黑色         | H6BPR-TGHC-PG16        | H6BPR HOOD,CENTER LOCKING,TOP ENTRY PG16,POWDER COATED,BLACK<br>H6BPR上壳,中部锁定,顶出PG16,黑色粉末喷涂                    | PG16                   |              |
| PART NUMBER<br>料号 | SURFACE TREATMEN<br>表面处理                 | PART DESCRIPTION<br>描述 |                                                                                                               | PG/M THREAD<br>PG/M 螺纹 | TYPE<br>类型   |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL  
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±-  
1 PLC ±-  
2 PLC ±-  
3 PLC ±-  
4 PLC ±-  
ANGLES ±-  
FINISH -

DWN  
Gino.Yao  
21MAY2015

CHK  
Chris.Wang  
21MAY2015

APVD  
Xiang.Xu  
21MAY2015

PRODUCT SPEC  
108-137014

APPLICATION SPEC  
114-137014

WEIGHT  
-

Customer Drawing

TE Connectivity

NAME  
H6BPR-TGHC-PG/M

SIZE  
A2

CAGE CODE  
-

DRAWING NO  
T192206XXXXX00

RESTRICTED TO  
-

SCALE  
1:1

SHEET  
2 OF 2

REV  
B

1471-9 (3/13)