






REV.	DATE	DESCRIPTION
NC	08/20/97	INITIAL RELEASE
A	12/10/07	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						12/10/07
6						CHECKED			PART DESCRIPTION SHIELDED CABLE PCB TERMINATION (FOR RG-58/U CABLE)				
5						ISSUED							
4						SHEET	1 OF 1		PART NO. 142197				
3													
2	FERRULE	COPPER	NICKEL	1				DWG. NO. 142197.DWG					
1	BODY	BRASS	NICKEL	1									
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE			C:/142/142197.DWG	REV. A	SIZE A	SCALE NA		