






2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE USE WITH THIS PRODUCT.
- PRODUCT IS REMOVED THE USB TYPE "C" FEMALE PORT USING THE SMARTKEEPER MASTER KEY (PANDUIT P.N.: SKMKEY).
- SEE INSTALLATION INSTRUCTION FOR PROPER USE OF PRODUCT.
- PARTS INCLUDES (DESCRIPTION: MATERIAL/COLOR):
 - EXTERNAL BODY SHELLS: POLYCARBONATE (PC), FLAME RATING: UL94 V-0/RED.
 - SMARTKEEPER INTERNAL BODY W/ UNIQUE FEMALE KEYED PATTERN, FLAME RATING: UL94 V-0/RED.
 - MAIN BODY CLIP: BRASS STEEL/NICKEL.
 - SMARTKEEPER SIDE SHIELD: BRASS STEEL/NICKEL.
 - USB TYPE "C" INTERNAL SUPPORT: POLYCARBONATE (PC), FLAME RATING: UL94 V-0/RED.
 - USB TYPE "C" SIDE EXTERNAL SHIELD: BRASS STEEL/NICKEL.
- PRODUCT IS DESIGNED FOR INDOOR USE ONLY.
- OPERATING TEMPERATURE AND HUMIDITY RANGE:
 - TEMPERATURE RANGE: -4°F (-20°C) TO +140°F (+60°C)
 - HUMIDITY RANGE: 10-70% NON-CONDENSING RELATIVE HUMIDITY.
- STORAGE CONDITIONS:
 - TEMPERATURE RANGE: -4°F (-20°C) TO +176°F (+80°C).
 - HUMIDITY RANGE: 10-80% NON-CONDENSING RELATIVE HUMIDITY.
- WEIGHT: 0.07 LBS/ (10) PCS [33.5 grams/ (10) PCS].
- DIMENSIONS IN [] ARE METRIC.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIALS RESTRICTIONS OF RoHs, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHs TECHNICAL ADAPTATION COMMITTEE.



SCALE 2:1

PART NUMBER		SKUSBC	
TITLE		SMARTKEEPER USB TYPE "C" BLOCKOUT DEVICE	
CUSTOMER DRAWING			
ITEM REVISION NAME		00402NAC/00	
DATASET FILE NAME		00402NAC_DC/00A	
 THIRD ANGLE PROJECTION			
MATERIAL			
SEE NOTES		00402NAC - DC	
DRAWN BY	DATE	CHK	SCALE
MDJR	04-25-19	DCS	2:1
SHEET 1 OF 1			SIZE
			A

2

1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	04-25-19	MDJR	DCS	MMR	DRAWING RELEASED	00402NAB-DC

A-SIZE CUSTOMER