



Pushing Performance  
Since 1945

# Han-Eco 16B-HSE-for DL-M25



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 43 016 0526                                                                        |
| Specification      | Han-Eco 16B-HSE-for DL-M25                                                            |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19430160526">https://b2b.harting.com/19430160526</a> |

## Identification

|                          |                |
|--------------------------|----------------|
| Category                 | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B     |
| Type of hood/housing     | Hood           |

## Version

|              |                      |
|--------------|----------------------|
| Size         | 16 B                 |
| Version      | Side entry           |
| Cable entry  | 1x M25               |
| Locking type | Double locking lever |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP66                                           |

## Material properties

|                                           |                                          |
|-------------------------------------------|------------------------------------------|
| Material (hood/housing)                   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                     |
| Material flammability class acc. to UL 94 | V-0                                      |
| RoHS                                      | compliant                                |
| ELV status                                | compliant                                |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| China RoHS                           | e                    |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Yes                  |
| California Proposition 65 substances | Naphthalene          |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels   | R22 (HL 1-3)         |
|                                      | R23 (HL 1-3)         |

## Specifications and approvals

|                |                                                |
|----------------|------------------------------------------------|
| Specifications | IEC 61984                                      |
|                | EN 45545-2 Fire protection on railway vehicles |
| Approvals      | CE                                             |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 147 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140178809                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |