



© 1962 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	A	REDRAWN & UPDATED PC-5561	10-16-69	Jmc
	B	BUTT WAS PARALLEL PC-5575	5-8-70	Jmc
	B1	REV PER ECR 05-013140	10/20/05	HL/m



BUSHING SLEEVE ASSY RING WIRE SPLICE

FOR .215 TO .255 WIRE INSULATION DIA.

1	RING	2-324385-1	ALUMINUM (QQ-A-250/1) COLOR: RED
2	BUSHING	21431-1	TEFLON (ASTM D3295) COLOR: NATURAL
1	WIRE SPLICE	328605	COPPER (QQ-C-576) GOLD PL (MIL-G-45204) TYPE 3 .0005 MIN THK OVER NICKEL PL (QQ-N-290) .0003 MIN THK
1	SLEEVE ASSY	329740	INSULATION: TEFLON (ASTM D3295) COLOR: NAT RING: ALUMINUM (QQ-A-250/1) COLOR: RED
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ± .008 ANGLES ± 5°		CONTRACT NO.	AMP
		DR.	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
		CHKD.	NAME: WIRE SPLICE
		APPROD.	POST INSULATED STRATO-THERM
MATERIAL SEE TABLE		REL.	MOISTURE SEAL - BUTT
		DSGN APPD.	WIRE SIZE: 8
		OTHER APPD.	SIZE: B
			CODE IDENT NO.: 00779
			NUMBER: 329716
		SCALE: NTS	SHEET: 1 OF 1