

## Han-Yellock bulkhead housing-Molly Bolts



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 300 0302
Specification	Han-Yellock bulkhead housing-Molly Bolts
HARTING eCatalogue	<a href="https://b2b.harting.com/11123000302">https://b2b.harting.com/11123000302</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Bulkhead mounted housing

### Version

Size	Han-Yellock® 30
Field of application	Hoods/housings for industrial applications
Pack contents	incl. 4 panel fastener

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	125 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140109872
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors