

Han-Eco 16B-HSE-for SL-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 016 0548
Specification	Han-Eco 16B-HSE-for SL-M40
HARTING eCatalogue	https://b2b.harting.com/19430160548

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Hood

Version

Size	16 B
Version	Side entry
Cable entry	1x M40
Locking type	Single locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 Fire protection on railway vehicles
Approvals	CE

Commercial data

Packaging size	1
Net weight	140 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140179509
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors