



Part number	GWOYBR-P07UD00-ROOL
Termination	pcb
Size	0
Locking principle	break , push
Coding	b_key_amc
Cable Diameter	cable amc 0


CODING:B




POSITIONS: 7 Positions




PANEL CUT OUT:



DIMENSIONS:



PCB-LAYOUT:



Number of contacts	7
Contact type	flat_contact
Contact diameter	06mm
Insulator material	peek
Termination	pcb
Termination diameter	05mm

Nominal current single contact	02_a	iec_60512_5_2
Nominal current insert	1,3 A	vde_0298_4
Test voltage	06_kv_ac	eia_364_20f

Degree of protection*	ipsk8_ip6k9k
Operating temperature	51_125_c
Mating cycles	5000

1/2

Material and surface treatments

Housing	ruthenium
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text