



Pushing Performance

# Han module adapter, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3011
Specification	Han module adapter, male
HARTING eCatalogue	<a href="https://b2b.harting.com/09140013011">https://b2b.harting.com/09140013011</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Adapter module
Description of the module	Han® Gigabit module
	Han® Shielded module
	Han® Megabit module

## Version

Gender	Male
--------	------

## Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +85 °C

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
California Proposition 65 substances	No

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	2
Net weight	5.69 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)