

NUTRECOMMEND PANEL CUT-OUT

NOTE:

MATERIAL

HOUSING: PA66 UL94V-0, BLACK
 CONTACT: BRASS
 NUT: BRASS
 SHELL: BRASS
 O-RING: EPDM

FINISH

CONTACT: 10 μ " GOLD PLATED
 NUT: OVER NICKEL
 SHELL: NICKEL PLATED
 O-RING: NICKEL PLATED

ELECTRICAL

RATED CURRENT: 16A
 RATED VOLTAGE: 63V
 WATER PROOF: IP67


ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

860-LP5-113R00Y

3 = BRASS/NICKEL SHELL & NUT
 S = STAINLESS STEEL (SS) SHELL & NUT

1 = GOLD FLASH
 4 = 10 μ " GOLD

P.C.B LAYOUT

UNITS = mm

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
 THE PROPERTY OF NorComp AND SHALL NOT
 BE REPRODUCED, COPIED OR USED AS THE
 BASIS FOR THE MANUFACTURE OR SALE OF
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADELDATE:
10/26/2020**NorComp**

SCALE: NTS	SHEET 1 OF 1	REV 3
------------	--------------	-------

DWG NO. 860-LP5-113R004