


NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.

CONNECTOR P/N	POSITIONS		CONTACT STYLE	CABLE O.D. RANGE
	#16	#20		
W8C80-6PG-513	2	4	CRIMP	0.13-0.15" (3.3 -3.8 mm)
W8C80-6PG-516			CRIMP	0.16-0.18" (4.1 -4.6 mm)
W8C80-6PG-519			CRIMP	0.19-0.21" (4.8 -5.3 mm)
W8C80-6PG-522			CRIMP	0.22-0.25" (5.6 -6.3 mm)
W8C80-6PG-528			CRIMP	0.26-0.285" (6.6 -7.2 mm)
W8C82-6PG-513			SOLDER	0.13-0.15" (3.3 -3.8 mm)
W8C82-6PG-516			SOLDER	0.16-0.18" (4.1 -4.6 mm)
W8C82-6PG-519			SOLDER	0.19-0.21" (4.8 -5.3 mm)
W8C82-6PG-522			SOLDER	0.22-0.25" (5.6 -6.3 mm)
W8C82-6PG-528			SOLDER	0.26-0.285" (6.6 -7.2 mm)



CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

PRELIMINARY

RoHS COMPLIANT

0A	PNK	01-19-16	PDR 14001 PRELIMINARY		
REV.	INIT.	DATE	DESCRIPTION		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY:	DATE:	 601 E. WILDWOOD VILLA PARK, IL 60181
			PNK	01-19-16	
			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 - CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			APPROVED BY:		TITLE: CABLE-TO-CABLE CONNECTOR 2-16 + 4-20 PIN CONTACTS MINI-CON-X POWER/SIGNAL CUSTOMER: STANDARD PRODUCT
			SCALE	SIZE	SHEET
			NTS	B	1 OF 1
			FILE:	DIRECTORY:	PART NUMBER:
			W8C8X-6PG-5XX_CD	SLW	W8C8X-6PG-5XX_CD
					REV 0A