





LOC		DIST		REVISIONS				
AF		50		REV	DESCRIPTION	DATE	OWN	APVD
				A1	REVISED PER ECR-12-011840	06JUL12	KH	KR

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 11.18±0.08 [0.440±0.003] CENTERS
- 2 SLOTS ACCEPTS 0.16 - 0.18mm [#34-#33] AWG COPPER MAGNET WIRE. TWO WIRES OF THE SAME SIZE MAX PER SLOT.
- 3 SLOT ACCEPTS A SINGLE 0.6mm [#22.5]AWG SOLID BARE COPPER WIRE
- 4 IDENTIFICATION NUMBER 3-22. 3 FOR THE MAGNET WIRE SLOT SIZE AND 22 FOR THE LEADWIRE SLOT SIZE
- 5 POINT OF MEASUREMENT, LOCATED APPROXIMATELY AS SHOWN



1742941-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR_RUTH 30NOV11	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK K_RANDOLPH 30NOV11	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K_RANDOLPH 30NOV11	TERMINAL, POSTED, DUAL IDC, MAG-MATE Slim Line	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± 0.13[.005]		SIZE	A1 00779	
3 PLC ± -		WEIGHT	1742941	
4 PLC ± -		SCALE	10:1	
ANGLES ± -		SHEET	1 OF 1	
MATERIAL 4M PRE-MILLED BRASS		FINISH 0.002032[.000080] MIN TIN PLATE	CUSTOMER DRAWING	
		RESTRICTED TO	REV A1	