





RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



Specification

Operating Life	1,000,000 cycles
Operating Force	F
Maximum Voltage	12 VDC
Max Current	50 mA
Dielectric Strength	250 V AC(1mn)
Contact Resistance	<100 mΩ
Insulation Resistance	>100M Ω
Bounce Time	<5 ms
Storage Temperature	-30° C to 85° C

F(force)

NO.	Force
M	180gf±50
K	250gf±50

H(height)

NO.	Height
43	4.3mm
43P	4.3mm with pegs
73	7.3mm
73P	7.3mm with pegs
85	8.5mm
85P	8.5mm with pegs
12	12mm
12P	12mm with pegs

X. ±0.50	X. ° ±2°	UNITS
.X ±0.30	.X° ±1°	mm
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH
		Q' TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS 125SJ X X

TITLE:
TACTILE SWITCH THT

APPD: ROGER

DWG NO. :
YTS 125SJ X X

CHKD: ROC

DR: BILLY WANG 2020/08/21

SCALE	SHEET	REV.
1/1	1/1	A1