




Specifications:
 规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage: 500V AC/minute
 耐受电压: 500V AC/分钟
 Temperature range: -40°C~+105°C
 温度范围: -40°C~+105°C
 Insulation resistance: 1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance: 20mΩ Max
 接触电阻: 20mΩ Max



X2001 H - 2xXX -PT V01
 ① ② ③ ④ ⑤

1. Series No
2. Category: H-Two-piece
3. Row No. Pin No: 2xXX-2x03-2x25P
4. Material: PT-PBT Glass Fiber UL94V-0
5. Plating: V01-Gold Flash

Poles	DIM A	DIM B
2x03	4.00	11.20
2x04	6.00	13.20
2x05	8.00	15.20
2x06	10.00	17.20
2x07	12.00	19.20
2x08	14.00	21.20
2x09	16.00	23.20
2x10	18.00	25.20
2x11	20.00	27.20
2x12	22.00	29.20
2x13	24.00	31.20
2x14	26.00	33.20
2x15	28.00	35.20
2x17	32.00	39.20
2x18	34.00	41.20
2x20	38.00	45.20
2x22	42.00	49.20
2x25	48.00	55.20



X2001H-2xXX-PTV01	PBT Glass Fiber	Brass	X2001W-A/X2001W-D
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 2.0mm IDC Connector
DWN	VIEW:	PART NO.: X2001H-2xXX-PTV01
CHKD	UNIT: mm/in	DWG NO.: X-X2001H-2xXX-PTV01
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED		SHEET
		1/1
		REVISION
		A0

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



广东星坤科技股份有限公司

DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn