


NOTES:

1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.



CONNECTOR P/N	POSITIONS		CONTACT STYLE	CABLE O.D. RANGE
	#16	#26		
W6A80-8SG-513	2	6	CRIMP	0.13-0.15" (3.3 -3.8 mm)
W6A80-8SG-516			CRIMP	0.16-0.18" (4.1 -4.6 mm)
W6A80-8SG-519			CRIMP	0.19-0.21" (4.8 -5.3 mm)
W6A80-8SG-522			CRIMP	0.22-0.25" (5.6 -6.3 mm)
W6A80-8SG-528			CRIMP	0.26-0.285" (6.6 -7.2 mm)
W6A82-8SG-513			SOLDER	0.13-0.15" (3.3 -3.8 mm)
W6A82-8SG-516			SOLDER	0.16-0.18" (4.1 -4.6 mm)
W6A82-8SG-519			SOLDER	0.19-0.21" (4.8 -5.3 mm)
W6A82-8SG-522			SOLDER	0.22-0.25" (5.6 -6.3 mm)
W6A82-8SG-528			SOLDER	0.26-0.285" (6.6 -7.2 mm)
NOTE: ADD SUFFIX "W" TO ANY CONNECTOR P/N ABOVE FOR WINGED COUPLING RING OPTION				

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

PRELIMINARY

0A		PNK		01-19-16		PDR 14001 PRELIMINARY							
REV.		INIT.		DATE		DESCRIPTION							
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF CONXALL CORPORATION. UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.						ORIG. DRAWN BY:		DATE:		conxall 601 E. WILDWOOD VILLA PARK, IL 60181			
						PNK		01-19-16					
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.						CHECKED BY:		TITLE: CABLE-END CONNECTOR 2-16 + 6-26 SOCKET CONTACTS MINI-CON-X POWER/SIGNAL CUSTOMER: STANDARD PRODUCT					
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16						APPROVED BY:		FILE: W6A8X-8SG-5XX_CD DIRECTORY: SLW PART NUMBER: W6A8X-8SG-5XX_CD					
△ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						SCALE		SIZE		SHEET			
						NTS		B		1 OF 1			

RoHS COMPLIANT