






DESCRIPTION: M5 FEMALE - FRONT PANEL MOUNT - SOLDER CUP - 4 POSITION



RECOMMEND PANEL CUT-OUT
MAX. PANEL THICKNESS: 0.075" [2.00]

NUT

NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
SHELL:
O-RING:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
NBR, BLACK

FINISH

CONTACT:

GOLD PLATED
OVER 50μ" NICKEL
NICKEL PLATED
NICKEL PLATED

NUT:
SHELL:

ELECTRICAL

RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:

1A
60V
100 MΩhms MIN.
10 mΩhms MAX.
IP67


ENVIRONMENT

OPERATION TEMPERATURE:
WIRE GAUGE:

-40°C TO +85°C
28 AWG MAX RECOMMENDED

851-004-203R00Y

1 = GOLD FLASH
4 = 10μ" GOLD



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
6

DWG NO.

851-004-203R00Y