

SUMMARY

Wires

Low voltage 13

Image is for illustrative purpose only

Series SP
Termination type Female print PCB
IP rating 50
AWG wire size 30.00 - 22.00
Cable Ø 0.00 - 0.00 mm
Status active
Matching parts [SAN.M13.GLA.3B](#)

Download

[Request a quote](#)
[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model *:
Keying 3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material Proprietary sulfone, gray
Variant B : White front nut
Weight 4.79 g

Performance

Configuration SP.M13 : 13 Low V.
Insulator L: PEEK (UL 94 / V-0/1.5)
Rated Current 4.0 Amps

Specifications

Contact Type: Print (straight)
Contact Dia.: 0.7 mm (0.028in)
R (max): 8.5 mOhm
Creepage distance min.: 0.5 mm

Others

Endurance (Shell): >2000 mating cycles

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Temp (min / max): -50 °C / +170 °C

DRAWINGS



RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.