

## SUMMARY

### # Wires

Low voltage 26



*Image is for illustrative purpose only*

Series	2P
Termination type	Female solder
IP rating	50
AWG wire size	34.00 - 28.00
Cable Ø	5.30 - 7.20 mm
Status	active
Matching parts	<a href="#">CAB.M26.GLA.C72G</a>

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	CR*: Free receptacle with cable collet
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	11.20 g

### Performance

Configuration	2P.M26 : 26 Low V.
Insulator	L: PEEK for solder contacts
Rated Current	2 Amps

### Specifications

Contact Type: Solder  
Contact Dia.: 0.5 mm (0.019in)  
Bucket Dia.: 0.5 mm (0.019in)  
Test voltage (kV rms) Contact-contact: 1  
Air clearance min.: 0.55 mm  
Creepage distance min.: 0.55 mm

### Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): >1000 mating cycles


Temp (min / max): -50°C / +150°C

F ret (min): 150 N

F ret (max): 250 N

Steam sterilization: 20 times

## DRAWINGS



### Dimensions

	A	L
mm.	18	52
in.	0,71	2,05

## RECOMMENDED BY LEMO

### Tools

### Cables

CMN.26.T28.070PGZE		Grey	
CMN.26.T28.070PNZE			
CMN.26.T30.054QGZE	TPR (medical)	Grey	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.