

Product data sheet

Characteristics

9001SKR9

Push button head, Harmony 9001SK, plastic, without mushroom, 30mm, 2 positions, push-pull



Main

Range of Product	Harmony 9001SK
Product or Component Type	Head for push-button
Device short name	9001SK

Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Octagonal
Type of operator	maintained
Light source	without
Light block supply	Without supply
Contacts type and composition	Without contact block
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03
IP degree of protection	IP64
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Cap/operator or lens colour	Without mushroom
Type of operator	Push-pull
Operator position information	2 positions
Size	30 mm

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	3389118036536
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	1.76 oz (49.895 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------