

## Hinged frame 12xMod a-I Han34HPR V-Hood



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 034 9975
Specification	Hinged frame 12xMod a-I Han34HPR V-Hood
HARTING eCatalogue	<a href="https://b2b.harting.com/09110349975">https://b2b.harting.com/09110349975</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Frame
Description of the accessory	for up to 12 single modules a ... I

### Version

Size	34 HPR
Pack contents	4x M4 screw 4x washer SK S4

### Technical characteristics

Tightening torque	1.5 Nm Fixing screws M4
-------------------	-------------------------

### Material properties

Material (accessories)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



**Pushing Performance**  
Since 1945

## Material properties

ECHA SCIP number 564b7d75-7bf6-4cfb-acb1-2168eb61b675

California Proposition 65 substances Yes

California Proposition 65 substances Lead  
Nickel

## Commercial data

Packaging size 1

Net weight 150 g

Country of origin Germany

European customs tariff number 85389099

GTIN 5713140194373

ETIM EC002310

eCl@ss 27440210 Fixing element for industrial connectors