

LC connector single mode 3mm




Image is for illustration purposes only. Please refer to product description.

Part number	20 10 125 8220
Specification	LC connector single mode 3mm
HARTING eCatalogue	https://b2b.harting.com/20101258220

Identification

Category	Contacts
Type of contact	LC contact
Description of the contact	Singlemode for cable diameter up to 3 mm

Version

Manufacturing process	Turned contacts
-----------------------	-----------------

Technical characteristics

Limiting temperature	-40 ... +75 °C
----------------------	----------------

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

Commercial data

Packaging size	2
Net weight	1.06 g
Country of origin	Germany
European customs tariff number	85367000
GTIN	5713140133648
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors