



P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL ISSUE	28AUG2020	SM	MZ
	2	INFORMATION ADDED TO SHEET 2	03SEP2020	SM	MZ
	A	PRODUCT UNDER TESTING	24NOV2020	SM	MZ



NOTES:

1. MATERIALS:
PLASTICS: PBT+PC ALLOY, UL-V0, UV-F1
CONTACTS: COPPER ALLOY, TIN PLATED
2. OPERATING RATINGS :
VOLTAGE (max): 600Vac Max
CURRENT (max): 25A ON 4.0mm² & 20A ON 12AWG
TEMPERATURE : -40°C TO 85°C
IP RATING : IP67 & IP68
3. FOR ASSEMBLY INSTRUCTIONS, REFER APPLICATION SPECIFICATION 114-133123
4. PACKAGING: MOQ 200 pcs IN PE BAG



POLARIZING KEY A
2379238-1
1-2379238-1


POLARIZING KEY B
2379238-2
1-2379238-2



KEYS



PRODUCT UNDER TESTING

CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT




BACKSHELL FOR
2379238-1
2379238-2

BACKSHELL FOR
1-2379238-1
1-2379238-2



2363547-2	2359419-2	KEY B	Ø 7 - Ø 10	IN-LINE PIN CONNECTOR	1-2379238-2
	2359419-1	KEY A			1-2379238-1
2363547-1	2359419-2	KEY B	Ø 10.5 - Ø 15		2379238-2
	2359419-1	KEY A			2379238-1
BACKSHELL P/N	HOUSING ASSY P/N	POLARIZING KEY	CABLE RANGE	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN SUBHASH. M 28AUG2020		 TE Connectivity								
CHK M. ZUCCA 28AUG2020			APVD PETER OTT 24NOV2020										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-133123		NAME NECTOR T, 3Pos, PIN CONNECTOR SCREW TYPE							
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±- 4 PLC ±- ANGLES ±1°		APPLICATION SPEC 114-133123									
MATERIAL - -		FINISH - -		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-2379238		RESTRICTED TO -	
CUSTOMER DRAWING								SCALE 2:1		SHEET 1 OF 2		REV A	

