


General information

Part number	W20K0C-P05MFG0-450S
Termination	solder
Size	0
Locking principle	push
Coding	0_key
Cable Diameter	cable_minj_45
Cable outlet	bend_relief




Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.

CODING: 0°



POSITIONS: 5 Positions



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	5
Contact type	pins
Contact diameter	07mm
Insulator material	peek
Wire cross section	22_awg
Termination	solder
Termination diameter	085mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	05_mm	05_mm
Nominal current single contact	075_a	iec_60512_5_2
Nominal current insert	5,625 A	vde_0298_4
Test voltage	06_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip68
Operating temperature	40_120_c
Mating cycles	5000

mated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text