

MATERIALS:

HOUSING:

CONTACTS:

NUT:

SHELL:


ORING:

PBT, UL94 V-0, BLACK
GOLD PLATED BRASS
(SEE P/N KEY BELOW)NICKEL PLATED BRASS
NICKEL PLATED BRASS
EPDM, BLACK

ELECTRICAL:


RATED CURRENT: 4A
RATED VOLTAGE: 250V
INSULATION RESISTANCE: 100 MOhms MIN.
CONTACT RESISTANCE: 10 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C
WATER PROOF: IP67

PANEL CUTOUT

NUT



NORCOMP MATING PART NUMBERS:


858-003-103RKT4*

858-R03-103RLU4*

858-R03-103RSS4*

*Also all material and contact plating variants

860-003-213R00Y

3 = BRASS/NICKEL SHELL & NUT
S = STAINLESS STEEL SHELL & NUT1 = GOLD FLASH
4 = 10u" GOLD

PCB LAYOUT

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03/07/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	SHEET 1	OF 1	REV 6
DWG NO.				860-003-213R00Y