

SUMMARY

Wires

Low voltage 7


Image is for illustrative purpose only

Series	4K
Termination type	Female crimp
IP rating	68
AWG wire size	16.00 - 12.00
Cable Ø	10.60 - 12.00 mm
Status	active
Matching parts	FGG.4K.307.CYCC11Z

Download

[Request a quote](#)
[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	PH*: Free receptacle, cable collet and nut for fitting a bend relief
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Variant	Z : Nut for fitting a bend relief
Weight	163.79 g

Performance

Configuration	4K.307 : 7 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated Current	20 Amps

Specifications

Contact Type:	Crimp
Contact Retention:	65 N
Contact Dia.:	2 mm (0.079in)
Bucket Dia.:	2.4 mm (0.094in)
Min. Conductor:	1.5 mm ² (AWG 16)
Max. Conductor:	2.5 mm ² (AWG 12)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

R (max): 3.3 mOhm

Vtest (contact-shell): 1350 V (AC), 1910 V (DC)

Vtest (contact-contact): 1500 V (AC), 2150 V (DC)

Others

Endurance (Shell): 5000 mating cycles

Temp (min / max): -55 °C / +200 °C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]


Climatical Category: 50/175/21

Shielding (min): 95 dB (10 MHz)

Shielding (min): 80 dB (1 GHz)

Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	A	L	S2
mm.	29	75,5	19
in.	1,14	2,97	0,75

RECOMMENDED BY LEMO

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Tools

Crimp Tool:	<u>DPC.91.101.A</u>
Crimp settings:	AWG/Selector = 12-14-16/8-7-6
Positionner:	<u>DCE.91.204.BVCM</u>
Extractor:	<u>DCC.91.202.5LA</u>
Replacement contact:	EGG.4B.675.ZZM
Spanner wrench:	<u>DCD.4E.050.PA190</u>

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.