

DESCRIPTION: M8 MALE - CABLE MOUNT - SOLDER CUP - 3 POS.

NOTE:

MATERIAL

HOUSING:

CONTACT:

NUT:

SHELL:

O-RING:

FINISH

CONTACT:

NUT:

SHELL:

ELECTRICAL

RATED CURRENT:

RATED VOLTAGE:

INSULATION RESISTANCE:

CONTACT RESISTANCE:

WATER PROOF:

ENVIRONMENT

OPERATION TEMPERATURE:

MAX WIRE AWG:

PBT UL94V-0, BLACK

BRASS

SEE P/N KEY

SEE P/N KEY

NBR, BLACK

GOLD PLATED

OVER 50 μ " NICKEL

SEE P/N KEY

SEE P/N KEY

3A

60V



100 M Ω hms MIN.

10 m Ω hms MAX.

IP67

-40°C TO +85°C




24



03 = BRASS/NICKEL (B/N) SHELL & NUT
0S = (B/N) SHELL & STAINLESS STEEL NUT
SS = STAINLESS STEEL SHELL & NUT

854-003-103RLSY

1 = GOLD FLASH
4 = 10 μ " GOLD



RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

6

DWG NO.

854-003-103RLSY