





DESCRIPTION: M12 FEMALE - PANEL MOUNT (REAR) - 8 POS.



PANEL CUTOUT



NUT



NOTE:

MATERIAL

HOUSING:

CONTACT:

NUT:

SHELL:

O-RING:

FINISH

CONTACT:

NUT:

SHELL:

ELECTRICAL

RATED CURRENT:

RATED VOLTAGE:

INSULATION RESISTANCE:

CONTACT RESISTANCE:

WATER PROOF:

ENVIRONMENT

OPERATION TEMPERATURE:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
EPDM, BLACK

GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED
NICKEL PLATED


2A
30V
100 MOhms MIN.
10 mOhms MAX.
IP67

-40°C TO +85°C

860-008-213R00Y

3 = BRASS/NICKEL SHELL & NUT
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH
4 = 10µ" GOLD



PCB LAYOUT

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

UNITS = INCHES [MM]



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-07-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

860-008-213R00Y