

BU-2641-D-XX-@**(Multiple Feature Test Prod to Unshrouded Banana Plug)**

- The BU-2641-D is a multiple feature test prod to unshrouded banana plug.
- Hookup wire is 18 AWG 65/36 tinned copper with temperature-resistant PVC insulation rated to 90°C.
- Material:

Needle	304 stainless-steel
Banana Plugs	Beryllium copper
Housing	Glass-filled nylon
- Ratings:

Current	10 Amps
Voltage	600V
- Length: The “XX” in the model number indicates length in inches.
Available lengths: 29”, 48”
- Color: The “@” in the model number indicates color.
Available colors: -0 Black, -2 Red
- RoHS 3 compliant