


SOIC-36 to DIP-36 SMT Adapter (1.27 mm pitch, 10.16 mm body)


REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		8.00				
B		3.50				
C		0.60				
D		0.67				
E		1.27				
F					0.600	
G					0.100	
H					0.025	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)