





Note:

Electrical

Current Rating:0.3A max

Contact Resistance:50m Ω max(Initial),75m Ω max(After)

Dielectric Withstanding Voltage:150VAC 1 Minute

Insulation Resistance 500mega ohms min. at 100 VDC

Physical

Housing:thermoplastic, UL 94V-0 rated,inWhite Color

Contact: Copper alloy

Operating Temperature:-40°C to +85°C

Model	PIN	DIM A	DIM B	DIM C	DIM D
BTB0.530-10PLBDC-M41	10	4.60	2.00	3.10	4.10
BTB0.530-12PLBDC-M41	12	5.10	2.50	3.60	4.60
BTB0.530-14PLBDC-M41	14	5.60	3.00	4.10	5.10
BTB0.530-20PLBDC-M41	20	7.10	4.50	5.60	6.60
BTB0.530-22PLBDC-M41	22	7.60	5.00	6.10	7.10
BTB0.530-24PLBDC-M41	24	8.10	5.50	6.60	7.60
BTB0.530-30PLBDC-M41	30	9.60	7.00	8.10	9.10
BTB0.530-32PLBDC-M41	32	10.10	7.50	8.60	9.60
BTB0.530-36PLBDC-M41	36	11.10	8.50	9.60	10.60
BTB0.530-40PLBDC-M41	40	12.10	9.50	10.60	11.60
BTB0.530-50PLBDC-M41	50	14.60	12.00	13.10	14.10
BTB0.530-60PLBDC-M41	60	17.10	14.50	15.60	16.60
BTB0.530-80PLBDC-M41	80	22.10	19.50	20.60	21.60

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DF12 SOCKET	
DECIMALS:		PAR	
ANGLES:		DWN	
.X ± 0.35		CHKD	
.XX ± 0.25		APVD	
.XXX ± 0.10		SCALE:1:1	
CUSTOMER COPY		UNIT:MM	
		SIZE:A4	
		SHEET:1F1	
		REV:A	