







PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	I/O

MICRO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



MICRO SIM



PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05


一、材质和镀涂:

1. 胶芯: LCP, UL 94V-0, 黑色
2. 端子: 磷铜C5210-H, T=0.15, 全区镍底30u"MIN 触点镀金GOLD FLASH0.6-1.0u" 焊脚双面镀亮锡50-80u"
3. 定位脚: 磷铜C2680-H, T=0.20, 全区镍底30u"MIN, 镀亮锡50-80u"
4. 外壳: 不锈钢 T=0.2

二、技术参数:


接触电阻: 100MΩ MAX
绝缘阻抗: 1000MΩ MIN(500DC)
额定电流: 每个接触件1A MAX
额定电压: 30V MAX(DC)
耐压: 500V R.M.S/MIN
使用温度: -40℃~85℃
湿度: 80% R.H MAX
寿命: >3000次

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.:±0.50	X':±2°	PART NO. ASIM-01A-6P	TITLE: MICRO SIM CARD HINGED 6PIN H1.8 掀盖式
X.X:±0.30	X.X':±1°		
X.XX:±0.20		DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	
MATERILA	---	APPD: Ava	SCALE N:A
FINISH	---		
			SHEET 1/1




NOTES

1. 每卷包装数量: 1200PCS/每卷
2. 卷带包装方式:



3. 每箱包装数量: 12000PCS/箱
4. 纸箱 350mm*350mm*440mm (内部尺寸), 材质 K=K



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.50	X'.:±2°	PART NO. ASIM-01A-6P	TITLE: MICRO SIM CARD HINGED 6PIN H1.8 横立式 包装图		
X.X:±0.30	X.X'.:±1°				
X.XX:±0.20					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			