RoHS Compliant 2011/65/EU

Compliant Halogen Free

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN









PIIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
CD	Detect Switch
C5	GND
C6	VPP
C7	I/O

CRICUIT DIAGRAM FOR CARD DETECT SWITCH





NOTES:

1.MATERIAL:
- HOUSING: High Temperature Thermoplastic
- Terminal: Copper Alloy
- Sheel: Stainless Steel

2.PLATING:
- Terminal:50u" Ni UNDERPLATED OVERALL
- G/F PLATED ON CONTACT AREA AND SOLDER AREA
- Sheel:30u" Ni UNDERPLATED OVERALL
- G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.TECHNICAL SPECIALITY:
- RATED VOLTAGE: 30V AC MAX.
- CURRENT RATING: 0.5A MAX.
- INSULATION RESISTANCE:1000MΩ MIN
- CONTACT REISTANCE:50mΩ MAX
- WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES
- OPERATING TEMPERATURE: −40℃~+85℃
- Humidity 80% R.H MAX

4.DIMENSIONS WITH MARK" * "MUST BE MEASURE BY QC AND IPQC



NANO SIM CARD



RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)

RECOMMENDED MATAL MASK T=0.12mm

SMT SOLDER AREA

NO PATTERN AND VIA HOLE IN HTIS AREA

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.:±0.35	X°.:±2°	PART NO. CSIM-1351-7P	TITLE: NANO SIM CARD 1.37H PUSH PUSH 有柱
.X:±0.15	.X°:±1°		
.XX:±0.10	.XX°:±0.5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	SCALE N:A / SHEET 1/1
MATERILA	— — —	APPD: Ava	
FINISH	— — —		

RoHS Compliant 2011/65/EU

Compliant Halogen Free

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN







1	CSIM-H137-7P	1500	10		15000	350X350X340
ITEM	PRODUCT NO	QTY/REEL	REEL/CARTON	Kg/CARTON	QTY/CARTON	CARTON SIZE

TOLERANCE	
X.:±0.35	X°.:±2°
.X:±0.15	.X°:±1°
.XX:±0.10	.XX°:±0.5°
UNITS	mm
MATERILA	— — —
FINISH	— — —

深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO. CSIM-1351-7P	TITLE: NANO SIM CARD 1.37H PUSH PUSH 有柱
DESIGN: Ethan	MANUFACTURE DWG
CHED: Olvia	SCALE N:A / SHEET 1/1
APPD: Ava	