







NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
2.TERMINAL:PHOSPHOR BRONZE
PLATING:1μ" GOLD FLASH OVERALL 50~100μ"NICKEL UNDER PLATED.



3D VIEW



RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

Model	PIN	DIM A	DIM B	DIM C	DIM D
BTB0.550-4PWBDC-G41	4	2.50	0.50	2.50	1.70
BTB0.550-6PWBDC-G41	6	3.00	1.00	3.00	2.20
BTB0.550-8PWBDC-G41	8	3.50	1.50	3.50	2.70
BTB0.550-10PWBDC-G41	10	4.00	2.00	4.00	3.20
BTB0.550-12PWBDC-G41	12	4.50	2.50	4.50	3.70
BTB0.550-14PWBDC-G41	14	5.00	3.00	5.00	4.20
BTB0.550-16PWBDC-G41	16	5.50	2.50	5.50	4.70
BTB0.550-18PWBDC-G41	18	6.00	4.00	6.00	5.20
BTB0.550-20PWBDC-G41	20	6.50	4.50	6.50	5.70
BTB0.550-22PWBDC-G41	22	7.00	5.00	7.00	6.20
BTB0.550-24PWBDC-G41	24	7.50	5.50	7.50	6.70
BTB0.550-26PWBDC-G41	26	8.00	6.00	8.00	7.20
BTB0.550-28PWBDC-G41	28	8.50	6.50	8.50	7.70
BTB0.550-30PWBDC-G41	30	9.00	7.00	9.00	8.20
BTB0.550-32PWBDC-G41	32	9.50	7.50	9.50	8.70
BTB0.550-34PWBDC-G41	34	10.00	8.00	10.00	9.20
BTB0.550-36PWBDC-G41	36	10.50	8.50	10.50	9.70
BTB0.550-38PWBDC-G41	38	11.00	9.00	11.00	10.20
BTB0.550-40PWBDC-G41	40	11.50	9.50	11.50	10.70
BTB0.550-42PWBDC-G41	42	12.00	10.00	12.00	11.20
BTB0.550-44PWBDC-G41	44	12.50	10.50	12.50	11.70
BTB0.550-46PWBDC-G41	46	13.00	11.00	13.00	12.20
BTB0.550-48PWBDC-G41	48	13.50	11.50	13.50	12.70
BTB0.550-50PWBDC-G41	50	14.00	12.00	14.00	13.20
BTB0.550-52PWBDC-G41	52	14.50	12.50	14.50	13.70
BTB0.550-60PWBDC-G41	60	16.50	14.50	16.50	15.70
BTB0.550-70PWBDC-G41	70	19.00	17.00	19.00	18.20
BTB0.550-80PWBDC-G41	80	21.50	19.50	21.50	20.70

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:0.5mm 侧插BTB
PLUG

PAR BTB0.550-XPWBDC-G41

DECIMALS:

ANGLES:

.X±0.25

±1°

.XX±0.15

.XXX±0.05

CUSTOMER COPY

DWN

CHKD

APVD

SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A