






SPECIFICATIONS

- 1.CURRENT RATING: 0.3A .
- 2.VOLTAGE RATING 30V AC/DC.
- 3.TEMPERATURE RANGE:-35°C TO +85°C
- 4.CONTACT RESISTANCE: 90mΩ MAX.
- 5.INSULATION RESISTANCE: 50 MΩ MIN.
- 6.WITHSTANDING VOLTAGE: 100V AC/MINUTE.



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

PIN	A	B	C
BTB0.415-10PLBDR-M41	4.6	1.6	1.0
BTB0.415-12PLBDR-M41	5.0	2.0	
BTB0.415-20PLBDR-M41	6.6	3.6	
BTB0.415-24PLBDR-M41	7.4	4.4	1.2
BTB0.415-30PLBDR-M41	8.6	5.6	1.5
BTB0.415-34PLBDR-M41	9.4	6.4	2.3
BTB0.415-40PLBDR-M41	10.6	7.6	3.2
BTB0.415-50PLBDR-M41	12.6	9.6	
BTB0.415-60PLBDR-M41	14.6	11.6	
BTB0.415-70PLBDR-M41	16.6	13.6	
BTB0.415-80PLBDR-M41	18.6	15.6	
BTB0.415-90PLBDR-M41	20.6	17.6	
BTB0.415-100PLBDR-M41	22.6	19.6	

The product is high

H

BTB0.415-XPLBDR-M41 1.45

BTB0.420-XPLBDR-M41 1.95

BTB0.424-XPLBDR-M41 2.40

BTB0.429-XPLBDR-M41 2.90

BTB0.434-XPLBDR-M41 3.40

BTB0.439-XPLBDR-M41 3.90

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.40MM BTB SOCKET
			PAR BTB0.415-XPLBDR-M41
DECIMALS:	ANGLES:		DWN
X.:±0.50	X':±2°		CHKD
X.X:±0.35	X.X':±1°		APVD
X.XX:±0.25			SCALE 1:1
CUSTOMER COPY		SIZE: A4	UNIT: MM
		SHEET: 1F1	REV: A