










RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

NOTES:

- 1.HUOSING: PA9T HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 2.TERMINAL:PHOSPHOR BRONZE
PLATING:1μ" GOLD FLASH OVERALL 50~100μ" NICKEL UNDER PLATED.

The product is high	MATING HEIGHT	PLUG (H.)	SOCKET (H.)	F
BTB0.530-XPLBSC-G71	3.00	0.80	2.20	1.60
BTB0.535-XPLBSC-G71	3.50	1.30	2.20	1.60
BTB0.540-XPLBSC-G71	4.00	1.00	3.00	1.90
BTB0.545-XPLBSC-G71	4.50	1.00	3.50	1.90
BTB0.550-XPLBSC-G71	5.00	1.00	4.00	1.90
BTB0.555-XPLBSC-G71	5.50	1.00	4.50	1.90
BTB0.560-XPLBSC-G71	6.00	2.00	4.00	1.90
BTB0.565-XPLBSC-G71	6.50	2.00	4.50	1.90

Model	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTB0.550-4PLBSC-G71	4	3.70	0.50	1.56	2.40	4.00
BTB0.550-6PLBSC-G71	6	4.20	1.00	2.06	2.90	
BTB0.550-8PLBSC-G71	8	4.70	1.50	2.56	3.40	
BTB0.550-10PLBSC-G71	10	5.20	2.00	3.06	3.90	
BTB0.550-12PLBSC-G71	12	5.70	2.50	3.56	4.40	
BTB0.550-14PLBSC-G71	14	6.20	3.00	4.06	4.90	
BTB0.550-16PLBSC-G71	16	6.70	3.50	4.56	5.40	
BTB0.550-18PLBSC-G71	18	7.20	4.00	5.06	5.90	
BTB0.550-20PLBSC-G71	20	7.70	4.50	5.56	6.40	
BTB0.550-22PLBSC-G71	22	8.20	5.00	6.06	6.90	
BTB0.550-24PLBSC-G71	24	8.70	5.50	6.56	7.40	8.00
BTB0.550-26PLBSC-G71	26	9.20	6.00	7.06	7.90	
BTB0.550-28PLBSC-G71	28	9.70	6.50	7.56	8.40	
BTB0.550-30PLBSC-G71	30	10.20	7.00	8.06	8.90	
BTB0.550-32PLBSC-G71	32	10.70	7.50	8.56	9.40	
BTB0.550-34PLBSC-G71	34	11.20	8.00	9.06	9.90	
BTB0.550-36PLBSC-G71	36	11.70	8.50	9.56	10.40	
BTB0.550-38PLBSC-G71	38	12.20	9.00	10.06	10.90	
BTB0.550-40PLBSC-G71	40	12.70	9.50	10.56	11.40	
BTB0.550-42PLBSC-G71	42	13.20	10.00	11.06	11.90	
BTB0.550-44PLBSC-G71	44	13.70	10.50	11.56	12.40	
BTB0.550-46PLBSC-G71	46	14.20	11.00	12.06	12.90	8.00
BTB0.550-48PLBSC-G71	48	14.70	11.50	12.56	13.40	
BTB0.550-50PLBSC-G71	50	15.20	12.00	13.06	13.90	
BTB0.550-52PLBSC-G71	52	15.70	12.50	13.56	14.40	
BTB0.550-54PLBSC-G71	54	16.20	13.00	14.06	14.90	
BTB0.550-56PLBSC-G71	56	16.70	13.50	14.56	15.40	
BTB0.550-58PLBSC-G71	58	17.20	14.00	15.06	15.90	
BTB0.550-60PLBSC-G71	60	17.70	14.50	15.56	16.40	
BTB0.550-62PLBSC-G71	62	18.20	15.00	16.06	16.90	
BTB0.550-64PLBSC-G71	64	18.70	15.50	16.56	17.40	
BTB0.550-66PLBSC-G71	66	19.20	16.00	17.06	17.90	8.00
BTB0.550-68PLBSC-G71	68	19.70	16.50	17.56	18.40	
BTB0.550-70PLBSC-G71	70	20.20	17.00	18.06	18.90	
BTB0.550-72PLBSC-G71	72	20.70	17.50	18.56	19.40	
BTB0.550-74PLBSC-G71	74	21.20	18.00	19.06	19.90	
BTB0.550-76PLBSC-G71	76	21.70	18.50	19.56	20.40	
BTB0.550-78PLBSC-G71	78	22.20	19.00	20.06	20.90	
BTB0.550-80PLBSC-G71	80	22.70	19.50	20.56	21.40	
BTB0.550-82PLBSC-G71	82	23.20	20.00	21.06	21.90	
BTB0.550-84PLBSC-G71	84	23.70	20.50	21.56	22.40	
BTB0.550-86PLBSC-G71	86	24.20	21.00	22.06	22.90	8.00
BTB0.550-88PLBSC-G71	88	24.70	21.50	22.56	23.40	
BTB0.550-90PLBSC-G71	90	25.20	22.00	23.06	23.90	
BTB0.550-92PLBSC-G71	92	25.70	22.50	23.56	24.40	
BTB0.550-94PLBSC-G71	94	26.20	23.00	24.06	24.90	
BTB0.550-96PLBSC-G71	96	26.70	23.50	24.56	25.40	
BTB0.550-98PLBSC-G71	98	27.20	24.00	25.06	25.90	
BTB0.550-100PLBSC-G71	100	27.70	24.50	25.56	26.40	

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE: 0.5mm 双槽BTB
PLUG

PAR BTB0.550-XPLBSC-G71

DECIMALS:

ANGLES:

.X±0.25

±1°

.XX±0.15

.XXX±0.05

CUSTOMER COPY

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:1F1



REV:A