



NOTES:



- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.TERMINAL:PHOSPHOR BRONZE
PLATING:1μ" GOLD FLASH OVERALL 50~100μ" NICKEL UNDER PLATED.



3D VIEW



MATING HEIGHT:5.0mm



RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

12	13	14	15
MAPX	MODIFICATION	DATE	SCAW

Model	PIN	DIM A	DIM B	DIM C	DIM D
BTB0.550-4PWBDC-M41	4	3.50	0.50	2.52	2.20
BTB0.550-6PWBDC-M41	6	4.00	1.00	3.02	2.70
BTB0.550-8PWBDC-M41	8	4.50	1.50	3.52	3.20
BTB0.550-10PWBDC-M41	10	5.00	2.00	4.02	3.70
BTB0.550-12PWBDC-M41	12	5.50	2.50	4.52	4.20
BTB0.550-14PWBDC-M41	14	6.00	3.00	5.02	4.70
BTB0.550-16PWBDC-M41	16	6.50	2.50	5.52	5.20
BTB0.550-18PWBDC-M41	18	7.00	4.00	6.02	5.70
BTB0.550-20PWBDC-M41	20	7.50	4.50	6.52	6.20
BTB0.550-22PWBDC-M41	22	8.00	5.00	7.02	6.70
BTB0.550-24PWBDC-M41	24	8.50	5.50	7.52	7.20
BTB0.550-26PWBDC-M41	26	9.00	6.00	8.02	7.70
BTB0.550-28PWBDC-M41	28	9.50	6.50	8.52	8.20
BTB0.550-30PWBDC-M41	30	10.00	7.00	9.02	8.70
BTB0.550-32PWBDC-M41	32	10.50	7.50	9.52	9.20
BTB0.550-34PWBDC-M41	34	11.00	8.00	10.02	9.70
BTB0.550-36PWBDC-M41	36	11.50	8.50	10.52	10.20
BTB0.550-38PWBDC-M41	38	12.00	9.00	11.02	10.70
BTB0.550-40PWBDC-M41	40	12.50	9.50	11.52	11.20
BTB0.550-42PWBDC-M41	42	13.00	10.00	12.02	11.70
BTB0.550-44PWBDC-M41	44	13.50	10.50	12.52	12.20
BTB0.550-46PWBDC-M41	46	14.00	11.00	13.02	12.70
BTB0.550-48PWBDC-M41	48	14.50	11.50	13.52	13.20
BTB0.550-50PWBDC-M41	50	15.00	12.00	14.02	13.70
BTB0.550-52PWBDC-M41	52	15.50	12.50	14.52	14.20
BTB0.550-60PWBDC-M41	60	17.50	14.50	16.52	16.20
BTB0.550-70PWBDC-M41	70	20.00	17.00	19.02	18.70
BTB0.550-80PWBDC-M41	80	22.50	19.50	21.52	21.20

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:0.5mm 侧插BTB
SOCKET

PAR BTB0.550-XPWBDC-M41

DECIMALS:

ANGLES:

.X±0.25

±1°

.XX±0.15

.XXX±0.05

CUSTOMER COPY

DWN

CHKD

APVD

SCALE:1:1

SIZE:A4

UNIT:MM

SHEET:1F1

REV:A