





DATE CODE: WEEK YEAR



Accept 1.57±0.13mm thickness card



NOTES:

1.MATERIAL:

HOUSING:HIGH TEMPERATURE THERMOPLASTIC(SEE TABLE)
 TERMINAL:PHOSPHOR BRONZE OR BRASS.(SEE TABLE)

2.FINISH:

TERMINAL: 50u" NI PLATING OVER ALL;
 100u" MATTE Sn PLATING ON SOLDER TAIL;
 GOLD PLATING ON CONTACT AREA.

3.MECHANICAL SPEC:

DURABILITY : 50 MATING CYCLES.
 RETENTION FORCE : 0.40 kgf MIN PER PIN.
 MATING FORCE : 1.15N MAX PER PAIR.
 UNMATING FORCE : 0.15N MIN PER PAIR.

4.ELECTRICAL SPEC:

CURRENT RATING: 1.1A MIN PER PIN.
 CONTACT RESISTANCE: 30 MILLIOHMS MAX. INITIAL.
 INSULATION RESISTANCE: 1000 MEGOHMS MIN.
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN.

5.WAVE SOLDERING:

THE CONNECTOR SHALL BE MOUNTED ON THE PCB,
 THE TEMPERATURE OF THE SOLDER SHALL BE
 260±5°C AND IMMERSION DURATION 10±2 SECONDS.

6.RoHS COMPLIANT OR HALOGEN FREE COMPLIANT.




深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
 X.XX ±0.25
 X.XXX ±0.15

X' ±2° X.X' ±0.5°



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

PCI-E 36pin 传统导柱式

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW05-PCI36-155B

MOLD NO.

APPROVED BY:

邱国夷

DATE :



2014-02-23


DRAW NO:

HYC-PCI17072518

SHEET NO.

1 OF 1



 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣 DATE : 2014-02-23 CHECKED BY: 马跃 DATE : 2014-02-23	
 UNIT: mm [inch]		PART NAME: MINI PCI 36pin 传统圆柱式	
		PART NO. HYCW05-PCI36-155B	MOLD NO.
APPROVED BY: 邱国夷		DATE : 2014-02-23	DRAW NO: HYC-PCI17072518
SCALE:1:1	SIZE: A4	SHEET NO. 1 OF 1	