



接点表

CN1	CN2
01	01
02	02
03	03
04	04
05	05
06	06
07	07
08	08
09	09
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
SHELL	SHELL

CN1



CN2



注:

- 100%短/断路&错线测试条件;
- 导通阻抗 $\leq 10\Omega$, 绝缘阻抗 $\geq 5M\Omega$. 高压测试, DC 300V/10mS.
- 产品采用PCB板连接, 符合1.4版技术规范.
- 标有▲为重要量测尺寸.

5	外模	PVC胶料 45P 黑色	4.3G
4	内模	PVC胶料 45P 黑色	0.9G
3	内连接	PCB板 T=1.6MM	1PCS
2	连接器	HDMI 19P A(F) 铁壳镀金 PIN针镀金	1PCS
1	连接器	HDMI 19P A(F) 铁壳镀金 PIN针镀金	1PCS
序号	名称	材料	用量



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI 母转母带耳朵 180°
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW01-HDMI-284B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2211081439
			SHEET NO. 1 OF 1