









PCB LAYOUT(TOP VIEW)
(T=1.60mm)



备注:

1) 材质:

1-1 本体:LCP 94V-0 黑色

1-2 端子:C2680

1-3 外壳:C2680或SPCC

2) 镀层:

2-1端子:所有面镀镍, 接点镀金(参照料号编码),
焊脚镀锡50u"MIN,

3) 技术规格

3-1. 额定电压:40V

3-2. 额定电流:0.5A

3-3. 绝缘电阻:100兆欧最小

3-4. 接触电阻:30毫欧最大

3-5. 操作温度:-20度到85度

3-6. 插入力:44.1N Max

3-7. 拔出力:9.8~44.1N;

3-8. 耐久:10000次

4	STOPPLE	1	LCP	UL94V-0,BL
3	SHELL	1	C2680R&SPCC	PLATED NI
2	HOUSING	1	LCP	UL94V-0,BL
1	CONTACT	21	C2680R-H	PLATED Au
NO.	ITEM	Q'TY	DESCRIPTION	FINISH



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI A TYPE 立式贴片13.0H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW167-HDMI A19-130B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2407031859	SHEET NO. 1 OF 1