





3D View



SCALE:2/1



NOTE:

1.MATERIAL SPECIFICATION:

1.1.C5240 T=0.08±0.005MM

2.TEST REQUIREMENTS:

2.1.CONTACT RESISTANCE: 30mΩ MAX

2.2.VOLTAGE RATING: 12 V/AC/DC/MAX

2.3.RATED CURRENT: 1.0A/MAX

2.4.WELDING THRUST: ≥3.0 Kg

2.5.DURABILITY: 20000 TIMES

2.6.WORKING TEMPERATURE: -40°C~85°C




3.PLATING REQUIREMENTS:

3.1.OVERALL NICKEL PLATED BOTTOM 60-120U

3.2.SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 48 HOURS.

3.3.SWEAT TEST: 1, ≤5 CYCLE: NO CORROSION, NORMAL CHARGING FUNCTION AND PERFORMANCE 2, 6~30 CYCLE: CORROSION IS ALLOWED, CHARGING FUNCTION AND PERFORMANCE ARE NORMAL

3.4.ROHS, REACH, HF HALOGEN-FREE AND A SERIES OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05METAL MASK T=0.10
TOLERANCE ±0.05MM
(FOR REFERENCE ONLY)

(Max. Working position)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L3.40*W1.00*H2.70	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT341027A	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412181643	
			SHEET NO. 1 OF 1	